



Xingke Professional Li-ion Battery Co.,ltd

File No.: WI/JS-SPE-PCM-2-001
Ver: A/0
Date: 2011-8-24

Polymer Lithium Ion Battery Specifications

Model : XK-605068*3P PACK

Draft	
Checked	
Approval	

Tel: +86-755-84715111 Fax: +86-755-84715777 Postcode: 518129



Xingke Professional Li-ion Battery Co.,ltd.

Specifications for XK-605068*3P

Contents

PACK (XK-605068*3P)battery	3
1 PACK battery's basic Specifications and standards	3
2 BOM of packing battery	4
3 BOM of protect board	4
4 Protect board component and circuit picture	4
Appendix 1 Battery XK-605068*3P	5
1 Scope	5
2 Product and Model Name	5
3 Ratings	5
4 Outline Dimensions and Appearance	5
5 Performance	6
6 Dimensional Drawing of XK-605068*3P	8
Appendix 2	9
1 Handling Instructions	9
2 Period of Warranty	11
3 Handling InstructionsShipment	11
4 Amendment of this Specification	11

Note: This specification is valid for 6 months from the date of release. Because of the corresponding process changes and other factors that leads to the changes in the specifications, the product specifications should be assistant with new subjects.



Xingke Professional Li-ion Battery Co.,Ltd.

Specifications for XK-605068*3P

PACK (XK-605068*3P) battery

1. PACK batteries' basic Specifications and standards

	Item	Specifications	Note			
1.1	Nominal Voltage	3.7V				
1.2	Nominal Capacity	6000mAh	Discharge(0.2CmA) cut off Voltage 2.75V 。 Time≥285min			
1.3	Charge Voltage	4.2V				
1.4	Impedance Resistance of PACK	140mΩ (Max)				
1.5	charge method	C.C/C.V.	C.C./C.V.			
1.6	charge method	1.6.1 Standard Charge :0.2CmA	Charge Current : 1200mA			
		1.6.2 Quick Charge :0.3CmA	Charge Current : 1800 mA			
1.7	charge time	Standard Charge ≤6h	cut off current: 60mA			
		Quick Charge ≤4h	cut off current: 60mA			
1.8	Max. Charge Current	1800mA				
1.9	Max. Discharge Current	2000mA				
1.1	over discharge protect Voltage	2.4V±0.1V				
1.11	over charge protect Voltage	4.3±0.05V				
1.12	short circuit protect current	3.0±1.5A				
1.13	Operating Temperature	Charge 0~45℃	relative humidity: 45%~75%			
		Discharge -10~50℃				
1.14	Storage Temperature	1 months -10~40℃	advice: charge the cells with 50%~60% capacity before storage			
		6 months 0~30℃				
1.15	Weight	approx 123g (reference)				
1.16	PACK size (as the follow picture)	Length: L (MAX)	71mm			
		Width: W (MAX)	51mm			
		Thickness: T (MAX)	18.6mm			
		Wires' length outside the packed cell : L1	60 (-1+3) mm			
note	printing code according as XKTD rule or according as customer requirement.					
	File No.	WI/JS-SPE-PCM-2-001	Ver.	A/0	Spec. page	3/11



Xingke Professional Li-ion Battery Co.,ltd.
Specifications for XK-605068*3P

2. BOM of packing battery


No.	Item	Specifications	Num.	Unit	Note
2.1	Polymer Lithium Ion Cell	XK-605068*3P	1	PCS	
2.2	protect board	XK-5040	1	PCS	0
2.3	wire diameter	1007#24AWG	1	PCS	red
2.4	wire diameter	1007#24AWG	1	PCS	black

note about the PACK battery ,you can choose the ROHS authentication or no ROHS authentication.

3.BOM of protect board

No.	Item	Specifications	Num.	Unit	Note
3.1	protect board IC	DW01+	1	PCS	U1
3.2	protect board MOS	8205	1	PCS	U2

4.Protect board component and circuit picture





Xingke Professional Li-ion Battery Co.,Ltd.

Specifications for XK-605068*3P

Appendix 1 Battery XK-605068*3P

1 Scope

This specification is applied to Lithium Ion Battery manufactured by Xingke Professional Li-ion Battery Co.,Ltd.

2 Product and Model Name

2.1 Product: Polymer Lithium Ion Battery

2.2 Model Name: XK 425280

3 Ratings

Item		Rating	Note
3.1 Capacity	Standard	6000mAh	Discharge:0.2CmA (1200mA)cut off Voltage:2.75V for cell
3.2 Nominal Voltage		3.7V	
3.3 AC Impedance Resistance		≤40mΩ	
3.4 Discharge Cut-off Voltage		2.75V	
3.5 Charge Current		1200mA	Standard Charge
3.6 Charge Voltage		4.2V	
3.7 Max. Charge Voltage		4.25V	
3.8 Charge Time		Approx 5.5h	Charge: 1200mA
3.9 Max. Charge Current		2000mA	0.3CmA
3.10 Max. Discharge Current		2000mA	0.3CmA
3.11 Weight		Approx 122g	
3.12 Operating Temperature	Charge	0~+45℃	
	Discharge	-10~+50℃	
3.13 Storage Temperature	<1months	-10~+40℃	Recommended storage temperature: 25℃,at theshipment state
	> 6 months	0~+30℃	

4 Outline Dimensions and Appearance

4.1 Outline Dimensions

See attached drawing for XK-605068*3P(Fig.1).

Thickness: 6 MAX. (Measured with weighting 300gf at 25±5℃)

Width: 50.5 MAX. (Measured with weighting 300gf at 25±5℃)

Length: 68.5 MAX. (not including tabs)

This thickness will be swelling when high temperature storage or operation in high temperature.

4.2 Appearance

There shall be no such defect as scratch, flaw, crack, rust, leakage, which may adversely affectcommercial value of battery.



Xingke Professional Li-ion Battery Co.,Ltd.

Specifications for XK-605068*3P

5 Performance

5.1 Standard Test Conditions

Test should be conducted with new batteries within one month after shipment from our factory and the cells shall not be cycled more than five times before the test. Unless otherwise defined, test and measurement shall be done under temperature of $25\pm 5^{\circ}\text{C}$ and relative humidity of 45~85%. The test results are not affected evidently by such conditions of temperature $15\sim 30^{\circ}\text{C}$ or humidity 25~85%RH.

5.2 Measuring Instrument or Apparatus

5.2.1 Dimension Measuring Instrument

The dimension measurement shall be implemented by instruments with equal or more precision scale of 0.01mm.

5.2.2 Voltmeter

Standard class specified in the national standard or more sensitive class having inner impedance more than $10\text{ M}\Omega$.

5.2.3 Ammeter

Standard class specified in the national standard or more sensitive class. Total external resistance including ammeter and wire is less than $0.01\ \Omega$.

5.2.4 Impedance Meter

Impedance shall be measured by a sinusoidal alternating current method (1kHz LCR meter).

5.3 Standard Charge $25\pm 5^{\circ}\text{C}$

Test procedure and its criteria are referred as follows:

$0.5\text{CmA}=3000\text{mA}$

Standard Charging: Constant current charging at 0.5CmA (3000mA) to 4.2V, then constant voltage charging at 4.2V to cut-off current $\leq 0.02\text{CmA}$ (120mA), time ≤ 3.5 hours.

5.4 Rest Period

Unless otherwise defined, 30min, rest period after charge, 30min, rest period after discharge.

5.5 Initial Performance Test

Item	Measuring Procedure	Requirements
(1) Open-Circuit Voltage	The open-circuit voltage shall be measured within 24 hours after standard charge.	$\geq 4.13\text{V}$
(2) AC Impedance Resistance	The Impedance shall be measured in an alternating current method (1kHz LCR meter) after standard charge at $25\pm 5^{\circ}\text{C}$.	$\leq 40\text{m}\Omega$
(3) Minimum Capacity	The capacity on 1800mA discharge shall be measured after standard charge at $25\pm 5^{\circ}\text{C}$ (specified CS).	$\text{CS} \geq 6000\text{mAh}$



Xingke Professional Li-ion Battery Co.,ltd.

Specifications for XK-605068*3P

5.6 Electrical Performance

5.6.1 Temperature Dependence of Capacity (Discharge)

Cells shall meet the discharge capacity requirements listed in the below table under respective discharge temperatures. The capacities are to be measured with constant discharge current 0.2CmA (2.75V cut-off) after standard charge at $25 \pm 5^\circ\text{C}$.

Discharge Temperature	0°C	25°C	45°C
Discharge Capacity	≥50%	100%	≥95%

5.6.2 Cycle Life

30min rest period after standard charge, 0.2CmA discharge to a cut-off voltage of 2.75V, 30min rest period, the capacity shall be measured after 300 cycles of standard charge and 0.2CmA discharge to a cut-off voltage of 2.75V at $25 \pm 5^\circ\text{C}$.

Capacity ≥690mAh

5.6.3 Shelf Life

Item	Measuring Procedure	Requirements
Storage Characteristic 1	1 The capacity on 0.2CmA discharge shall be measured after standard charge and then storage at $25 \pm 5^\circ\text{C}$ for 30 days.	Remaining Capacity ≥ 85% CS
	2 After above measured Remaining capacity, the capacity on 0.2CmA discharge shall be measured after 0.2CmA charge.	Recovery capacity ≥ 90% CS
Storage Characteristic 2	1 The capacity on 0.2CmA discharge shall be measured after standard charge and then storage at $60 \pm 2^\circ\text{C}$ for 7 days.	Remaining Capacity ≥ 75% CS
	2 After above measured Remaining capacity, the capacity on 0.2CmA discharge shall be measured after 0.2CmA charge.	Recovery capacity ≥ 80% CS

5.6.4 Long Time Storage Characteristics

New battery, after about half charge after a period of storage at $25 \pm 5^\circ\text{C}$ no more than 3 months (storage 180 days without load at $25 \pm 5^\circ\text{C}$). The remaining available capacity is ≥ 80% CS. The capacity is determined with the capacity of the by the most of preceding three cycles. (0.2CmA charge or discharge)




Xingke Professional Li-ion Battery Co.,ltd.
Specifications for XK-605068*3P

5.7 Mechanical Performance

Item	Measuring Procedure	Requirements
Vibration test	After standard charge, the battery is to be tested as following conditions: Amplitude:0.8mm Frequency:10~55Hz(sweep:1Hz/min) Direction: X/Y/Z axis for 90~100min. The battery is to be tested in three mutually perpendicular to each axis.	No fire, no explosion, no smoking is obtained.
Drop Test	Drop the battery in the shipment condition(full-charge)from 1m height onto 5cm or thicker concrete with p-tile on it 3 times each of X, Y, and Z directions at $25 \pm 5^{\circ}\text{C}$	No fire, no explosion, no smoking is obtained.

6 Dimensional Drawing of XK-605068*3P





Xingke Professional Li-ion Battery Co.,ltd.

Specifications for XK-605068*3P

Item	Specifications
T (MAX)	6mm
W (MAX)	50.5mm
L (MAX)	68.5mm
L2	$1.25 \pm 1.0\text{mm}$
L3	$9 \pm 1\text{mm}$
W'	$42 \pm 1.5\text{mm}$
d	5mm
a1	$90 \pm 5^\circ$
a2	$90 \pm 5^\circ$

Appendix 2

1 Handling Instructions

Read and observe the following warnings and precautions to ensure correct and safe use of Li-ion batteries.

Danger!

Failure to observe the following precautions may result in battery leakage, overheating, explosion and /or fire.

- Do not immerse the battery in water or allow it to get wet.
- Do not use or store the battery near sources of heat such as a fire or heater.
- Do not use any chargers other than those recommended.
- Do not reverse the positive(+) and negative(-) terminals.
- Do not connect the battery directly to wall outlets or car cigarette-lighter sockets.
- Do not put the battery into a fire or apply direct heat to it.
- Do not short-circuit the battery by connecting wires or other metal objects to the positive(+) and negative(-) terminals.
- Do not carry or put the battery together with necklaces, hairpins or other metal objects.
- Do not strike, throw or subject the battery to severe physical shock.
- Do not pierce the battery casing with a nail or other sharp object, break it open with a hammer, or step on it.
- Do not directly solder the battery terminals.
- Do not attempt to disassemble or modify the battery in any way.
- Do not recharge the battery near a fire or in extremely hot conditions.

Warning!

Failure to observe the following precautions may result in battery leakage, overheating, explosion and/



Xingke Professional Li-ion Battery Co.,ltd.

Specifications for XK-605068*3P

or fire.

- Do not place the battery in a microwave oven or pressurized container.
- Do not use the battery in combination with primary batteries(such as dry-cell batteries) or batteries of different capacity, type or brand.
- Do not use the battery if it gives off an odor, generates heat, becomes discolored or deformed, or appears abnormal in any way. If the battery is in use or being recharged, remove it from the device or charger immediately and discontinue use.
- Keep the batteries out of the reach of children. If a child somehow swallows a battery , seek medical attention immediately.
- If the battery leaks or emits an odor, immediately remove it from the proximity of any exposed flame. The leaking electrolyte can ignite and cause a fire or explosion.
- If the battery leaks and electrolyte gets in your eyes, do not rub them. Instead, rinse them with clean running water and immediately seek medical attention. If left as is, electrolyte can cause eye injury.

Caution!

Do not use or store the battery where is exposed to extremely hot, such as under window of a car in direct sunlight in a hot day. Otherwise, the battery may be overheated. This can also reduce battery performance and/or shorten service life.

Use the battery only under the following environmental conditions. Failure to do so can result in reduced performance or a shorten service life. Recharging the battery outside of these temperatures can cause the battery to overheat, explode or catch fire.

Operating environment:

When charging the battery: 0°C ~45°C

When discharging the battery: -20°C ~60°C

When stored up to 30 days: -20°C ~45°C

When stored up to 90 days: -20°C ~35°C

In cases where children use the battery, instruct them on the contents of the user' s guide and keep an eye on them to ensure that the battery is being used correctly.

If the battery leaks and electrolyte gets your skin or clothing, immediately rinse the affected area with clean running water. If left as is, skin inflammation can occur.

For directions on battery installation and removal, read the instruction manual that accompanies the equipment in which the battery will be used.

If a device is not used for an extended period, the battery should be removed and stored in a cool, dry place. Otherwise, resting or reduced performance may occur.

If the terminals of the battery are dirty, wipe them clean with dry cloth before use. Otherwise, solid electrical contact may not be charged with the equipment, and this can cause power outages or charging to fail.



Xingke Professional Li-ion Battery Co.,ltd.

Specifications for XK-605068*3P

2 Period of Warranty

The period of warranty is one year from the date of shipment. Guarantees to give a replacement in case of cells with defects proven due to manufacturing process instead of the customers abuse and misuse.

3 Shipment

Partial charged condition.

4 Amendment of this Specification

This specification is subject to change with prior notice.